

As regulations and best practices become more stringent, it is important for manufacturing facilities to know the appropriate replacement schedule for elements that protect their process and product integrity. If a defined replacement schedule is not available for preventive maintenance of filtration elements, consider the following recommended replacement intervals.

HOUSING	REPLACEABLE PART TYPE	APPLICATION	RECOMMENDED REPLACEMENT INTERVAL				STEAM STERILIZATION CYCLES
			3 MOS	6 MOS	12 MOS	5 YRS	
 DF	B, V, M, S	Compressed air			X		
	A	Compressed air	X				
 SG, HD	SB, FF, MF, SMF, FFHTNX, MFHTNX, SMFHTNX	Compressed air			X		
	AK	Compressed air	X				
	SBP, FFP, MFP, SMFP	Compressed air			X		
 Drains	UFM-D, UFM-T, UFM-P, Service Kits	Condensate management				X	
 P-EG, PG-EG, P-BE	Lifetec™ P-SRF V, Lifetec™ P SRF X*, Lifetec™ PF-PT N	Sterile air, gas	X				Up to 150 cycles *Up to 250 cycles
	P-GS, P-GSL N	Steam, gas		X			Or after 6 cleanings
 P-FG, P-PT	PP-FC, PP-FC 100	Liquid	X				
	Lifetec™ PP N, Lifetec™ PP100 N, PP-TF N	Liquid		X			

HOUSING	REPLACEABLE PART TYPE	APPLICATION	RECOMMENDED REPLACEMENT INTERVAL				STEAM STERILIZATION CYCLES
			3 MOS	6 MOS	12 MOS	5 YRS	
	LifeTec™ PES-WN, LifeTec™ PES-BN-A	Liquid	X				Up to 100 cycles
	LifeTec™ P-GSL N	Liquid		X			Or 6 ultrasonic baths
	LifeTec™ PT N, P-FF, P-MF, P-SMF, P-SB	Compressed air, gas			X		
	P-AK	Gas	X				
	DF-S Ultrapleat	Compressed air	Every 3 months, check integrity with dryer screen for element status				
	Desiccant cartridges						
	Gaskets	Gaskets	At least every year or with every element replacement				

Important Notice

Many factors beyond the control of Donaldson can affect the use and performance of Donaldson products in a particular application, including the conditions under which the product is used. Since these factors are uniquely within the user's knowledge and control, it is essential the user evaluate the products to determine whether the product is fit for the particular purpose and suitable for the user's application. All products, specifications, availability and data are subject to change without notice, and may vary by region or country.



Donaldson Company, Inc.
Process Filtration
Minneapolis, MN

donaldsonprocessfilters.com
shop.donaldson.com

North America 800-543-3634
Mexico 800-343-3639
Fax 952-885-4791

processfilters@donaldson.com



F117067 ENG (01/21) Recommended Replacement Schedule – Preventive Maintenance

© 2017 Donaldson Co., Inc. All Rights Reserved. Donaldson and the color blue are marks of Donaldson Company, Inc. All other marks belong to their respective owners.
{Contains Donaldson proprietary technology.}